






4789-1




CONCENTRICITY GAUGES



4789-2A

to ensure the accuracy 2μm, the distance between measuring point and roller should be <30mm



- Accuracy 2μm
- Optional accessory: dial test indicator

Code	Applicable diameter	Remark
4789-1	Ø3.5mm-25mm	fixed stand, good rigidity
4789-2	Ø1mm-25mm	fixed stand, good rigidity
4789-3	Ø1mm-25mm	fixed stand, good rigidity
4789-1A	Ø3.5mm-25mm	universal stand, convenient operation
4789-2A	Ø1mm-25mm	universal stand, convenient operation
4789-3A	Ø1mm-25mm	universal stand, convenient operation

